

The Comfortable Precision Pliers & Cutters

Electronics pliers with cutting edges are designed especially for cutting soft to medium hard wires.

Precision ground cutting edges for smooth cuts

Glare free black finish



Lay-on, riveted precision joint

Light weight design for maximum user comfort in production work

C70 tool steel HR60 hardness

Electronic Diagonal Cutters



56812 Precision Electronic Diagonal Cutters, Narrow Shape Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. For absolutely flush cutting of copper wires in difficult to access locations. \leftarrow lbs. .19

Item No.	mm	Inch	Cut Capacity	Pkg.
56812	118	4.5	0.8mm/16AWG	1

Electronic Oblique 48° Cutter



56833 Electronic Oblique 48° Cutter Wide pointed head. Cutting edge - full flush. With cutting edge at 48° for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56833	138	5.5	1.3mm/16AWG	.22	1

Electronic Diagonal Cutters



56818 Precision Electronic Diagonal Cutters, Wide Pointed Head Cutting edge - full flush. With return spring. C70 special tool steel. For an absolutely flush cut of copper wire.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56818	138	5.5	1.3mm/16AWG	.22	1

Electronic Diagonal Cutters



56813 Precision Electronic Diagonal Full Flush Cutters With Wire Trapping Spring Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56813	128	5.0	1.0mm/16AWG	.19	1

Narrow Front Cutter/Long Nose Pliers



56830 Electronic Narrow 30° Front Cutter / Long Nose Pliers Extremely narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. Edge at 30° to face end of pliers for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56830	118	4.5	0.6mm/16AWG	.19	1

Electronic Diagonal Cutters



56815 Precision Electronic Diagonal Cutters, Wide Pointed Head Cutting edge - semi flush. With return spring. C70 special tool steel. Universal small diagonal cutter for cutting copper wires.

Item No.	mm	Inch	Cut Capacity	Hard Wire	Pkg.
56815	138	5.5	2.0mm/16AWG	0.8	1

Electronic Diagonal Cutters



56825 Precision Electronic Diagonal Cutters, Wide Shape With Wire Holding Spring Wide, Pointed head. Cutting edge - full flush. With return spring & fixture for holding ends of wires that have been cut off. For an absolutely flush cut of copper wire.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56825	138	5.5	1.3mm/16AWG	.23	1

Electronic Stripping Pliers



56871 Electronic Stripping Pliers Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#56871	mm	Inch	Ø	AWG	lbs.	Pkg.
	180	7.0	0.81-2.59	20-10	.15	1

Electronic Pointed Pliers



56801 Electronic Short Nose Precision Pliers Narrow, short head. Smooth jaws. Width at tip is only 1.2mm. C70 special tool steel. For holding small components as well as for holding and angling wires.

Item No.	mm	Inch	Pkg.	lbs.
56801	138	5.5	1	.23