

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1122190018](#)
Status: **Active**
Overview: Woodhead ArcArrest Connector System
Description: Woodhead ArcArrest Receptacle with Handle and Drawplates, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7, Three Grommets Included

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E145922

General

Product Family Wiring Devices
 Series [112219](#)
 IP Rating IP69K
 NEMA Configuration N/A
 Overview [Woodhead ArcArrest Connector System](#)
 Product Literature Order No 987651-4741
 Product Name ArcArrest
 Receptacle Type Single
 Specialty Switch-Rated
 Type Receptacle
 UPC 78172558524
 Woodhead Yes

Physical

Cord Grip Body Size F4 1"
 Flange Yes
 Flip Lid Yes
 Gender Female
 Length 199.08mm (7.838")
 Locking Blade N/A
 Net Weight 98.540/g
 Poles 2

Electrical

Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V / 250V AC

Material Info

Engineering Number ARC30FHDAB04

Reference - Drawing Numbers

Sales Drawing 1122190024-000



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018)
 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[112219 Series](#)