

eao  **EAO AG**
Tannwaldstrasse 88
4600 Olten
Switzerland

Phone: +41 62 286 9111
info@eao.com

Part No. 82-5151.1125, Illuminated Pushbutton

19mm, Illuminated Pushbutton, Stainless steel, Flush/Flat, Plug-In Terminal, Silver Contacts, Momentary, Ring Illumination, Blue LED, 110VAC



Specifications	
Actuator	<u>Illuminated pushbutton</u>
Size	19 mm
Action	Momentary
Illumination	Ring Illumination
LED Color	Blue
LED Voltage	110 VAC
Contact Type	SPDT
Contacts	SPDT
Contact Material	Silver Contacts
Actuator Color	Silver
Mounting Type	Panel Mount
Terminal	Plug-in terminal

Housing Material	Stainless steel
Switching Function	On-Off
Environmental Rating	IP65, IP67
Impact Resitance (According to IEC 62262)	IK 10
Mechanical Life	1'000'000 switching cycles
Operating Temperature [Min]	-30 °C
Operating Temperature [Max]	70 °C
AC Contact Current Rating	3 A
DC Contact Current Rating	1 A
AC Voltage	240 V
DC Voltage	240 V