

LS01660

Rated Power	2 Watt
Maximum power	5 Watt
Impedance	4 + 8 Ohm
Sound pressure level	-
Sensitivity	-
Frequency response (-10 dB)	150 - 20000 Hz
Mean sound pressure level	84 dB (1 W / 1 m)
Max sound pressure level	-
Maximum cone displacement	4 mm
Resonance frequency	320 Hz
Magnetic induction	0,75 Tesla
Magnetic flux	65 micro Weber
Height of front pole-plate	2 mm
Voice coil diameter	14 mm
Height of winding	3,0 mm
Cutout diameter	45 mm

