









Polished brass







- This luminaire is compatible with bulbs of the energy classes: A++ to E
- Fitting is rated at 50W max

874/2012

- Pressed steel construction
- Supplied with ceramic GU10 & GU5.3 lampholders
- Hole cut out 70-140mm: replaces a wide range of outdated downlights
- Shallow profile: neat, unobtrusive solution
- Converts traditional mains R50, R64 and R80 downlight and eyeball dimensions to modern GU10 or low voltage lighting: allows use of modern light source without expensive repairs & decoration
- M.O.M: 5 / O.P.Q: 40

Code	Colour	Wattage	IP Rating
CR80BS	Polished Brass	50W Max	IP20
CR80CR	<b>Polished Chrome</b>		
CR80SN	Brushed Nickel		
CR80WH	White		









