



### 2 Models available



Powered by Rechargeable

**LI-ION**  
Technology



Powered by 3x



### Rechargeable

#### HT340R Key features:

- Rechargeable Li-ion head torch
- 340 Lumens light output
- 200m beam
- 3 Light modes: spot, wide beam and distance dimming
- Rechargeable via USB cable
- Runtime: 3hr 30min high | 78hrs low
- Supplied with: USB charging cable

#### Optional extras:

- AC/DC vehicle charging adaptors
- Helmet clips

### Non Rechargeable

#### HT180 Key features:

- Powered by 3 x AAA batteries
- 180 Lumens light output
- 100m beam
- 3 Light modes: spot, wide beam and distance dimming
- Runtime: 3hrs high | 130hrs low



PRODUCT CODE	DIMENSIONS
NSHT340R	(L)144X(D)60X(H)230mm



PRODUCT CODE	DIMENSIONS
NSHT180	(L)144X(D)60X(H)230mm