

LED Filament Series



VT-1966

HIGHLIGHTS :

WATTS



6

EQ. WATTS



60

LUMINOUS



500

BEAM ANGLE



300

Item No	:	VT-1966
SKU Code	:	4362
Watts	:	6
EQ. Watts	:	60
Base / holder	:	E27
Voltage	:	220-240V,50Hz
Lumen(lm)	:	500
Color Temperature	:	2200K
Beam Angle	:	300
Commercial type	:	ST64
PF	:	>0.5
LED Chip Type	:	FILAMENT
CRI	:	>80
Energy rating label	:	A+
Certification	:	CE,EMC,ROHS
IP Rating Protection Class	:	IP20
Body type	:	GLASS
Dimmable	:	No
Life Time	:	>20000 Hours
Operation Temperature	:	-25 ~50°C
EAN code	:	3800157602754
Unit size	:	D:58x139mm
Packing details	:	50.00
Unit cbm	:	0.00020

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb