

BASICS



POWER

provides power where you need it most

FEATURES

- · Ideal for domestic and office use
- Four sockets for connecting devices
- Thermal cut-out prevents risk of fire caused by power overload
- · Premium white gloss finish
- Manufactured to BS EN 61242




PRODUCT IMAGES



SATT0413/4W

LINE DIAGRAMS







PRODUCT INFORMATION

Part Number SATTx13/4W

Part Number Note x = length of cable in metres

Product Dimensions Height 200mm x Width 200mm x Depth 66mm

Sockets 4

TECHNICAL SPECIFICATIONS

CE

Standard(s)	This product is certified to applicable British safety standards
	BS EN 61242
Maximum Load (Wound)	720 Watts, 240 Volts
Maximum Load (Unwound)	13A: 3120 Watts, 240 Volts
IF IN DOUBT CONSULT A QUALIFIED ELECTRICIAN	

SAFETY WARNING

PLEASE READ CAREFULLY AND USE IN ACCORDANCE WITH OUR SAFETY INSTRUCTIONS BELOW

Uncoil cable before use

Position the cable carefully to avoid accidents

X DON'T Use in wet conditions

DON'T Allow heavy tools etc to hang unsupported on the cable or from the socket

DON'T Remove the plug and wire directly into a mains supply

DON'T Exceed the total maximum load.