



DATA SHEET

2 WAY METAL RCD INCOMER CONSUMER UNIT

Catalogue Reference :- NMRS206/40, NMRS206/63, NMRM206/40, NMRM206/63

Image not to scale



Dimensions

Height	185mm
Width	130mm
Box Depth	80mm
Total Depth	104mm

Current Rating	40A or 63A
Operating Voltage	240Volts +10/-6%
Short Circuit Rating	16kA when protected by a 100A HRC fuse to BS1361
Insulation Voltage	500Volts AC
IP Rating	IP2XC
Consumer Unit	BSEN 61439-3
Main Switch	BSEN 60947-3
RCD Incomer	BSEN 61008
Colour	RAL 9010
Box Material	Steel
Lid Material (including visor)	Steel
Outgoing Terminal Size Neutral Bar	Maximum cable Size 10mm
Outgoing Terminal Size Earth Bar	Maximum cable size 10mm
Incoming Terminal Size Neutral Bar	Maximum cable size 16mm
Incoming Terminal Size Earth Bar	Maximum cable size 16mm
Incoming Switch Disconnecter Size	Maximum cable size Main Switch 50mm, RCD 35mm

Replacement Incoming devices

- **WRS60/2** (63A 30mA RCD)
- **WRS40/2** (40A 30mA RCD)
- **WRM60/2** (63A 100mA RCD)
- **WRM40/2** (40A 100mA RCD)

Replacement Spare Items

- **B4471/SPARE** (user operating instructions)
- **NHLABELPACK** (Full Kit of Labels)
- **NM4/MCLA** (complete lid assembly)

Compatible Circuit Protection Devices:			
MCBs		RCBOs	
6kA B curve (3-5In)	6kA C curve (5-10In)	6kA B curve (3-5In)	6kA C curve (5-10In)
NHXB06	NHXC06	NHXSBS1B06	NHXSBS1C06
NHXB10	NHXC10	NHXSBS1B10	NHXSBS1C10
NHXB16	NHXC16	NHXSBS1B16	NHXSBS1C16
NHXB20	NHXC20	NHXSBS1B20	NHXSBS1C20
NHXB32	NHXC32	NHXSBS1B32	NHXSBS1C32
NHXB40	NHXC40	NHXSBS1B40	NHXSBS1C40
NHXB50	NHXC50	NHXSBS1B50	NHXSBS1C50