

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Cordless Combi

GSB 18-2-LI Plus

Best price/performance ratio among professional cordless combis

The most important data

Battery voltage	18 V
Max. drilling diameter in masonry	13 mm
Max. screw diameter	8 mm

**Part number:** 0 601 9E7 102[> More product information](#)

Technical data


Torque, max. (hard/soft)	63 / 24 Nm
No-load speed (1st gear / 2nd gear)	0 – 500 / 0 – 1.900 rpm
Chuck capacity, min./max.	1,5 / 13 mm
Drill spindle thread	1/2"
Battery voltage	18 V
Battery capacity	2,0 Ah
Weight incl. battery	1,54 kg
Torque settings	20+1
Length	202,0 mm
Height	230,0 mm
Drilling diameter	
Max. drilling diameter in wood	38 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in masonry	13 mm
Screw diameter	
Max. screw diameter	8 mm

Noise/vibration information

Screwdriving	
Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²
Impact drilling in masonry	
Vibration emission value ah	13.5 m/s ²
Uncertainty K	1.5 m/s ²
Drilling in metal	
Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Power tools for trade & industry
Advantages:

- Attractive solution for the entry-level segment of professional applications
- Keyless chuck with 13mm bit holder for common accessories
- New ergonomics: Better handling due to compact design
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and deep discharge
- Electronic Motor Protection (EMP) protects the motor against overload and ensures a long lifetime
- Integrated LED light for illuminating the work area, even in dark places


Prices / Scope of delivery

Part number	0 601 9E7 170	0 601 9E7 102
1/2 L-BOXX inlay for accessories 1 600 A00 2WC	✓	-
1/2 L-BOXX inlay for tool 1 600 A00 2WA	✓	✓
2 x 2.0 Ah Li-Ion batteries 1 600 Z00 036	✓	-
AL 1820 CV quick charger 2 607 225 426	✓	-
Carton (L-BOXX-ready)	-	✓
L-BOXX 136 1 600 A00 1RR	✓	-