

LLCDI18022

18V 2-Speed Hammer/Drill/Driver

Features

- Combination Drill, Screw Driver and Percussion drill to suit multiple applications
- 13mm keyless chuck for greater accessory compatibility
- Quick adjustment 24 torque settings for perfect screwdriving every time
- 2 gears for most materials and applications
- Electronic variable speed, reverse and brake for total control



SPECIFICATION (1)	LLCDI18022
Sound pressure level (dB(A))	88.5
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	99.5
Sound power level uncertainty [dB[A]]	3
Vibration screw driving [m s ²]	0.7
Vibration screw driving uncertainty [m s ²]	1.5
Vibration drilling into Metal [m s ²]	1.4
Vibration drilling into metal uncertainty [m s ²]	1.5
Vibration drilling into concrete [m s ²]	15
Vibration drilling into concrete uncertainty [m s ²]	1.5
No load speed gear 1 (rpm)	400
No load speed gear 2 (rpm)	1550
Max. torque (Nm)	50
Torque settings	24
Voltage (V)	18
Battery pack capacity (Ah)	1.3
Battery type	Li-ion
Supplied in	Tool bag
Charger supplied	45 min
No. of batteries supplied	2
percussion rate gear 1	6000
percussion rate gear 2	23250
Article Number	5133001955
Weight with battery pack (kg)	1.93
Max drilling steel (mm)	13
Max. drilling wood (mm)	38
Max. drilling masonry (mm)	13
Chuck capacity (mm)	13