

Product information

18V COMBI DRILL LXT



Satisfying the professional's needs

DHP459Z

Voltage	18 v
Max. in wood	38 mm
Max. in masonry	13 mm
Max. in steel	13 mm
Max Torque S/H	25 / 45 Nm
Torque Settings	16 + drill
Battery Type	Lithium-ion
Vibration: Drilling	8 m/sec ²
Vibration K factor	1.5 m/sec ²
Body only machine	1
Net weight	1.5 - 1.8 kg
Electric Brake	1
Variable Speed Control	Trigger
Blows per Minute	0-22500/6000 bpm
No Load Speed	0-1500/400 rpm



BL MOTOR **BRUSHLESS** **LITHIUM-ION**

- Compact design with an overall length of only 192mm.
- Single sleeve keyless chuck allows for easy bit installation/removal by one hand.
- LED Job light with pre-glow function.
- BLDC motor specially designed to provide, above all, more work amount on a single full battery charge.

Details correct as of: 2-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com