

0 601 8B5 001 – GOP 12V-28

Material number	0 601 8B5 001	0 601 8B5 002	0 601 8B5 070
EAN	3165140842501	3165140842488	3165140842532
1 x Starlock BIM plunge cut saw blade All 65 APB, Curved-Tec, Wood + Metal 2 608 661 781			✓
1 x Starlock BIM plunge cut saw blade All 65 BSPB, Curved-Tec, Hard Wood 2 608 662 017			✓
1 x Starlock BIM plunge cut saw blade AIZ 20 AB, Wood + Metal 2 608 661 640			✓
1 x Starlock BIM plunge cut saw blade AIZ 32 APB, Wood + Metal, Curved-Tec 2 608 661 644	✓	✓	✓
1 x Starlock BIM segment saw blade ACZ 85 EB, Wood + Metal 2 608 661 636			✓
1 x Starlock HCS plunge cut saw blade AIZ 32 EPC, Curved-Tec, Wood 2 608 661 637			✓
1 x Starlock delta sanding plate AVZ 93 G 2 608 000 493			✓
2 x battery GBA 12V 2.5Ah 1 600 A00 4ZL			✓
5 x sanding sheets, K 2x80, 2x120, 1x240 2 608 621 104			✓
Cardboard box	✓		
L-BOXX 102 1 600 A00 1RP		✓	
L-BOXX 136 1 600 A00 1RR			✓
Quick charger GAL 1230 CV 1 600 A01 16B			✓
Packaging dimensions (width x length x height)	220 x 340 x 80 mm	360 x 440 x 110 mm	360 x 440 x 155 mm
Battery voltage	12.0 V	12.0 V	12.0 V
Weight incl. battery	1,0 kg	1,0 kg	1,0 kg
Battery capacity			2,5 Ah



Technical data

Technical data

Battery voltage	12 V
No-load rotation	5.000 – 20.000 opm
Oscillation angle on left and right	1,4 °
Weight excl. battery	0.81 kg

Noise/vibration information

Sound pressure level	79 dB(A)
Sound power level	90 dB(A)
Uncertainty K	3 dB



Sales information

Positioning

- The most compact cordless multi-tool in the Bosch Starlock category

User benefit incl. Reason to believe

- Superior Starlock interface of optimised 3-dimensional tight connection for highest direct power transfer
- Smallest handle grip makes it very ergonomic and easy to operate
- Lightweight design for comfortable handling and convenience of use