

Product information

18V Reciprocating Saw LXT



DJR186Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Capacity in Wood	255 mm
Capacity in Mild Steel Pipe	130 mm
Strokes per Minute	0 - 2,800 spm
Stroke Length	32 mm
Noise sound pressure	84 dB(A)
Noise sound power	95 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	12.5 m/sec ²
Vibration: Cutting Chipboard	13.0 m/sec ²
Net weight	3.5 - 3.8 kg



LITHIUM-ION

- Tool-less blade change.
- Trigger switch with lock-off lever
- Electric brake
- Variable speed
- Ergonomically designed handle
- Newly designed crank mechanism for higher efficiency
- High power

Details correct as of: 9-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com