

DEWALT XR FLEXVOLT Metal Reciprocating Blade 5 Piece Set 152mm 14/18TPI DT99553-QZ



- Increased efficiency for maximum cordless run time
- Up to 2 X longer life compared to standard blades
- Improved longer run time
- Variable tooth designs provide increased blade efficiency and a reduction of tooth breakage
- Tough Coat reduces friction and heat build up
- Constructed from M42 high speed steel

Description:

The DEWALT XR FLEXVOLT Metal Reciprocating Blade 5 Piece Set 152mm 14/18TPI, has been designed for increased efficiency and maximum run time. The blade can last up to 2x longer compared to a standard construction blade. With variable tooth design the blades have increased efficiency which reduces tooth breakage. The bi-metal blades are coated with a special Tough Coat finish which reduces friction and heat buildup for longer life. The blades have been optimised to fit XR FLEXVOLT power tools for high demanding jobsite operations.

Specifications	
Kit Contains	5 Pieces
Application	Metal
Cutting Length	152 mm
Number of Teeth per Inch	14/18 TPI
Blade material	M42 High Speed Steel

Supplied With:

 5 x 152mm (6") 14/18 TPI Metal Saw Blades