



DWE6423

125MM RANDOM ORBIT SANDER

Selling Proposition

- 280 Watt variable speed motor adjusts from 8,000-12,000 orbits per minute, providing ideal sanding speed for all materials
- Low vibration allowing for extended usage without fatigue
- Built in dust extraction port allowing direct connection to dust extractor, or DEWALT AirLock system
- Textured anti-slip top and body grip provides ultimate comfort and control during use
- Dust-sealed switch prevents contamination
- Controlled finishing system controls pad speed and minimises gouging during start up

Standard Equipment

- Fabric dust bag with built-in extractor ports

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	280 Watts
Power Output	120 Watt
Orbits Per Minute	8,000 - 12,000 opm
Orbit Size	2.6 mm
Paper Size	125 mm
Pad Size	
Weight	1.28 kg
Length	170 mm