



## SOCKET SETS

S560

### SOCKET SETS 1/4" AND 1/2"



- 1/4" and 1/2" socket set
- High performance alloy steel
- Matt finish
- ISO 1174
- DIN 3120
- Case: High Density Polythene (HDPE)
- Contents, 56 pcs
  - 12 pcs 1/4" bi-hex sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
  - 10 pcs 1/4" bi-hex deep sockets: 4, 5, 6, 7, 8, 9, 10, 11, 12, 13 mm
  - 13 pcs 1/2" bi-hex sockets: 10, 11, 12, 13, 14, 15, 17, 19, 22, 24, 27, 30, 32 mm
  - 3 pcs 5/16" bits TORX® T 45, 50, 55
  - 1 pc 1/4" magnetic adaptor
  - 1 pc 1/4" magnetic adaptor
  - 2 pcs 1/4" extension bars 50 mm / 2" & 100 mm / 4"
  - 1 pc 1/4" sliding T-bar 100 mm / 4"
  - 1 pc 1/4" universal joint
  - 1 pc 1/4" spinner with 2-component handle
  - 1 pc 1/4" bit holder
  - 1 pc 1/4" bit adaptor
  - 2 pcs 1/2" extension bars 125 mm / 5" & 250 mm / 10"
  - 1 pc 1/2" universal joint
  - 1 pc 1/2" spark plug socket hex 21 mm (13/16")
  - 1 pc 1/2" T-adaptor
  - 1 pc 1/2" x 5/16 bit holder
  - 3 pcs L-Keys hex 1.5, 2, 2.5 mm
  - 1 pc 1/4" ratchet, 72 teeth / 5° action angle, quick release, slim head
  - 1 pc 1/2" ratchet, 72 teeth / 5° action angle, quick release, slim head

S560	731415 0122264	4	375x215x100	4665