

0 600 8A3 B00 – AMW SG

Material number	0 600 8A3 B00
EAN	3165140649544
Packaging dimensions (width x length x height)	126 x 103 x 794 mm
Top seller	0.0



Technical data

Technical data

Cut length	26 cm
Chain speed	12 m/s
Drive link thickness	1,3 mm
Weight	1,6 kg

Functions

Auto-oiling system for chain lubrication	✓
--	---

Noise/vibration information (tree pruner attachm.)

Sound pressure level	84.5 dB(A)
Sound power level	104.5 dB(A)
Uncertainty K	2.5 dB

Sales information

Positioning

- Pole pruner attachment for the AMW 10 multi-tool: the compact chainsaw for working overhead

User benefit

- High chain speed of 12 m/s
- Auto-oiling system for chain lubrication
- Compact blade with 26 cm cutting length for overhead cutting

Highlights

- AMW Multi-tool. The all-purpose tool for the all-purpose lifestyle.