

UNILITE USB RECHARGEABLE FLASHLIGHTS

HV-FL9R
/ FL7R

LIGHT BY
CREE
LEDs

USB
CHARGING

- » HV-FL9R 1100 Lumen white CREE LED
- » HV-FL7R 450 Lumen white CREE LED
- » Built in USB rubberised charging point with Micro-USB cable (included)
- » Hard anodized die cast matte aluminium body
- » Tactical rubberised micro switch operation
- » 3 light mode settings and 8Hz defence strobe
- » Flawless smooth reflector for long distance beam
- » Water resistant IPX7 - 1m submersible
- » Impact resistant to 1m
- » Nylon velcro holster (included)
- » Safety nylon wrist strap (included)

HV-FL9R

BATTERY 3.7v 2600 mAh 18650 Li-ion Battery (inc.)
WEIGHT 200g (with battery)
DIMENSION 139 x 33mm

HV-FL7R

BATTERY 3.7v 800 mAh 14500 Li-ion Battery (inc.)
WEIGHT 93g (with battery)
DIMENSION 113 x 30mm



POUCH AND USB CABLE (INC.)



AIRCRAFT ALUMINIUM HOUSING



RECHARGEABLE BATTERY (INC.)



USB RECHARGEABLE

Upgraded



4½-80
HOURS
RUNTIME

270
METRE
BEAM RANGE

1100
LUMENS
OUTPUT

IPX7
WATER
PROOF

Upgraded



2-20
HOURS
RUNTIME

210
METRE
BEAM RANGE

450
LUMENS
OUTPUT

IP67
DUST & WATER
PROOF