

HV-RL4

UNILITE RUBBER WEATHERPROOF LANTERN



BEAMASTER
Lense®

10
HOURS
RUNTIME

250
METRE
BEAM RANGE

300
LUMENS
OUTPUT

IP54
DUST & WATER
RESISTANCE



EASY PUSH BUTTON
MICRO SWITCH



REAR CHARGING POINT



OPTICAL BEAMASTER LENS



WEATHERPROOF

- » 300 Lumen white Seoul LED
- » Synthetic industrial grade rubber housing
- » Rear charging point for use with Unilite PS-RB2LION rechargeable battery
- » Floats beam upright in water
- » Ultra tough polycarbonate reflector
- » Optical Beamaster lens for beam penetration
- » Contoured rubber easy grip handle
- » Rubber moulded push micro switch
- » Highly robust build quality
- » IP54 dust and water resistant

BATTERY 1 x 6v PJ996 (not included)
WEIGHT 506g (without battery)
DIMENSION 180 x 110 x 125mm