

PS-L2


UNILITE LED FLOATING LANTERN

BEAMASTER
LENS®
10
 HOURS
 RUNTIME

250
 METRE
 BEAM RANGE

300
 LUMENS
 OUTPUT

IP56
 DUST+WATER
 RESISTANCE


MAGNIFYING BEAMMASTER LENS



EASY PRESS SWITCH



OPTIONAL COLOURED LENSES



SMALL & COMPACT

- » 300 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Robust and weatherproof
- » Floats beam upright in water
- » Optical Beammaster lens for beam penetration
- » Ultra tough polycarbonate reflector
- » Rubber moulded push micro-switch
- » High-vis yellow for added safety
- » Contoured easy grip handle
- » Impact resistant to 1m
- » IP56 dust and water resistant

BATTERY 1 x 6v PJ996 Lantern Battery (not included)
WEIGHT 254g (without battery)
DIMENSION 175 x 105 x 115mm