

UNILITE LED SWIVEL HEADED LANTERN

PS-L3
/ L3RK



BEAMMASTER
LENS

10
HOURS
RUNTIME

- » 300 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Optical Beamaster lens for beam penetration
- » Swivel head rotation 135°
- » Easy screw battery replacement
- » Side charging point for use with PS-RB2LION
- » Impact resistant to 1m

250
METRE
BEAM RANGE

300
LUMENS
OUTPUT

IPX4
WATER
RESISTANCE

BATTERY 1 x 6v PJ996 Lantern Battery (not inc.)
WEIGHT 449g (without battery)
DIMENSION 170 x 115 x 255mm



WALL BRACKET (INC.)



CARRY STRAP (INC.)

PS-L3RK UNIVERSAL KIT

Rechargeable Kit including:

- » PS-L3 LED Lantern
- » PS-RB2LION 3.6v Li-ion 2600mAh Battery
- » DC-USB-KIT Charging Kit (inc UK, EU & AUS plugs)
- » 5v DC-USB Cable
- » 12v USB Car Adaptor
- » Carry Strap with Carabiners
- » Wall Mounting Bracket

