

UNILITE USB RECHARGEABLE INSPECTION LIGHT

PS-IL10R



- » 27x White Samsung SMD LEDs - 1000 lumen
- » Additional 250 lumen torch in the head
- » Ultra strength aluminium and polycarbonate housing
- » Integral hanging hook and strong magnet for hands-free use
- » Multi positional hook / foldable kick stand
- » DC-USB charging cable included for portable non-static charging
- » Red-to-Green charging indicator light
- » Operating Temperature: -5 °C to +40 °C
- » Protection Class: IP54 (do not submerge)
- » Impact Resistant to 1m

3-32
HOURS
RUNTIME

64
METRE
BEAM RANGE

1000
LUMENS
OUTPUT

IP54
DUST & WATER
RESISTANCE

BATTERY 3.7v 5000 mAh lithium-ion rechargeable battery (included)

WEIGHT 338g (with battery)

DIMENSION 205 x 60 x 42 mm



DC-USB CABLE (INCLUDED)



USEFUL MAGNET AND HOOK



SMOOTH EVEN LIGHT SPREAD



250 LUMEN TORCH HEAD



PROFESSIONAL LIGHTING GUIDE