



## Flashni - Sounder with Xenon Beacon

---

Part Number: FL/BL/W/D 12v

The Flashni is an audible and visual device which requires one single installation point. This greatly reduces installation costs and is less obtrusive than two separate devices. Versions are available with the sounder and beacon linked, or with separate terminals for independent operation.



### Technical Specifications:

Voltage:	9 - 15Vdc (12Vdc version) 18 - 28Vdc (24Vdc version) (*1)
Current:	110mA 12Vdc version (Typical Tone 5) 68mA 24Vdc version (Typical Tone 3)
Sound Output:	103dB(A) 12Vdc version (Typical Tone 5 ) 101dB(A) 24Vdc version (Typical Tone 3)
Tones:	42
Volume Control:	10dB
Flash Rate:	1Hz
Flash Power:	0.7j
Temperature:	- 10°C to + 55°C
Monitoring	Reverse polarity
Construction:	ABS/PC lens
Protection:	IP54 (s)* IP65 (d)*
Weight:	0.33Kg
Colour:	Red or White
Lens Colour:	Red, Amber, Clear, Green or Blue

(\*1) 110 / 230Vac when used with a Deep powered base.

(s)\* Shallow Base

(d)\* Deep / U Base

Features:

- 32 tones (user selectable)
- 12V or 24V
- Secure clip fit base
- Volume control
- Fire approved and Signalling tone options
- For Fire, Security and Signalling
- Quick fitting for easy installation
- Reduce output to suit application