



OD Series Water Resistant Speakers - 125.050UK



Water resistant speakers for panel mounting, suitable for PA installations in swimming pools, bathrooms etc.

- 2-way speakers
- 5cm (2") tweeter with mylar cone
- IP35 rated
- Plastic enclosure
- Spade terminal connections (6mm)
- Woofer with polypropylene cone
- Built-in crossover
- Includes fixing kit
- Gasket included
- Supplied in pairs
- Humidity max.:95%
- Dispersion angle: 140°
- Temperature range: -20 - 85°C

	125.050UK
Colour	Black
Impedance	8 ohms
Speaker size	165mm (6.5")
Frequency response	80Hz - 20kHz
Power max.	100W
Power rms	40W
Magnet weight	221g (7.8 oz)
Cutout	132mmØ
Mounting depth	65mm
SPL @ 1W/1m	87dB
Dimensions	84.5 x 180mmØ
Weight	745g

