



Full Range Horn Speaker – FRH50 / 952.066UK



ABS full range horn speaker with 6.5" reverse mounted LF driver and front mounted 1" dome tweeter housed in an IP65 rated UV stabilised enclosure. Unlike standard outdoor horn speakers, this powerful unit has a full range output and is therefore suitable for background music as well as public address.

- Full range music quality output
- 4 volume tapings inside rear compartment
- Long throw coverage
- Integral mounting bracket

LF driver	165mmØ (6.5") reverse woofer	Dispersion angle	90°
HF driver	25mm (1") phenolic dome tweeter	Sensitivity @ 1W/1m	99dB (±3dB)
IP rating	IP65	Impedance : 100V	2.6k, 1.3k, 666, 333 Ohms
Frequency response	90Hz - 20kHz	Tappings	3.75W, 7.5W, 15W, 30W
Power rating : max.	50W	Dimensions	370 x 270 x 330mm
Power rating : rms	30W	Weight	3.56kg