IMPULSE

Counter Displays

TITAN

6-in-1 Screwdriver 11010

- Chrome vanadium bits with magnetic tips
- Ergonomic soft grip handle for maximum comfort

 Contains: (4) screwdriver tips: #1 & #2 Phillip and 1/4" & 3/16" Slotted; (2) Nutdrivers: 1/4" & 5/16"

UPC	Master	Inner	
8-02090-11010-8	48	6	



High-Torque Ratcheting Screwdriver 11014

- 3 way ratcheting action: forward, reverse and lock
- Includes 7 screwdriver bits and bit storage
- sizes:
- 2 Phillips #1, #2
- 2 Slotted 3/16, 1/4
- 1 Square S1, S2
- 2 Star T15, T20





UPC	Master	Inner	
8-02090-11014-6	48	12	

Fits-All-Phillips Screwdriver 11009

- Patented, precision ground tip design fits a variety of screw sizes
- Chrome plated S2 Alloy steel shaft has fits-all-phillips on one end and 1/4" slotted at other end
- Ergonomic TPR comfort handle for maximum grip and user comfort
- Interactive counter display features assorted screws to demonstrate fits-all tip

UPC	Master	Inner
8-02090-11009-2	80	10



Telescoping Magnetic Pickup Tool

- Powerful magnet features shielded sides for targeted pickups
- Comfortable textured cushion grip ideal for retrieving dropped parts, fasteners and tools
- Ships in 20pc counter display

Part #	Capacity	Length	UPC	Master	Inner
11763	3 lb	5-1/2"-21-7/8"	8-02090-11763-3	120	20
11663	5 lb	6-1/2"-33"	8-02090-11663-6	120	20
11716	16 lb	7-3/4" to 30-3/4"	8-02090-11716-9	120	20

