



2831-B606  

## Bit set slimBit electric

Slotted, Phillips, 6-pcs. in box

**Flexible, compact, mobile.**

Order No. 42212



### Product Highlights:

#### Increases your efficiency

Extensive interchangeable blade system saves you space.

#### Offers you full protection

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

#### Increases your safety

Wiha slimBits ensure unrestricted and fully insulated access to low-lying screws.

### Description

When combined with Wiha slimVario products, the insulated slimBits can effortlessly reach even low-lying screws and spring elements thanks to the Wiha slimTechnology specially developed for electric applications.

### Application

For all work on or around electrical components up to 1,000 V AC. Ideal for pressing fastening and spring elements.

## Standards

Manufactured acc. to IEC 60900.

## Note

SlimBits are designed to be used with slimVario tools, so they are not suitable for fitting to machines. 6 mm slimBits only to be used in the slimVario® bit holder and slimTorque VDE bit holder (VDE torque system).

## Set constituent

---

- 1x Bit slimBit electric , Slotted: 6,5 , Bit length: 75
- 1x Bit slimBit electric , Slotted: 2,5 , Bit length: 75 \*
- 1x Bit slimBit electric , Slotted: 5,5 , Bit length: 75
- 1x Bit slimBit electric , Phillips: PH1 , Bit length: 75
- 1x Bit slimBit electric , Phillips: PH2 , Bit length: 75
- 1x Bit slimBit electric , Slotted: 3,5 , Bit length: 75

\* no slim version