

# CR-M110AC3



CR-M110AC3 Pluggable interface relay 3c/o, A1-A2=110VAC, 250V/10A

## General Information

Extended Product Type	CR-M110AC3
Product ID	1SVR405612R7000
EAN	4013614497612
Catalog Description	CR-M110AC3 Pluggable interface relay 3c/o, A1-A2=110VAC, 250V/10A
Long Description	The CR-M110AC3 pluggable interface relay is from the CR-M (miniature) relay range. This relay operates with a 110 V AC rated control supply voltage and has a 3 c/o (SPDT) output with contacts rated at 250 V / 10 A. The relay has an integrated orange test button for manual actuation and locking of the output contacts. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories.

## Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

## Popular Downloads

Data Sheet, Technical Information	2CDC117002D0204
Instructions and Manuals	1SVC405600M9000

## Dimensions

Product Net Width	21.2 mm
Product Net Height	35.6 mm
Product Net Depth / Length	27.5 mm
Product Net Weight	0.033 kg

## Technical

Function	Pluggable miniature interface relay CR-M
Sub-Function	Relay w/o built in LED
Output	3 c/o (SPDT) contacts
Output Signal	250 V / 10 A
Rated Control Supply Voltage (U <sub>s</sub> )	110 V AC

## Environmental

