

**TERMSERIES**  
**ZQV 1.5N/R6.4/19 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



TERMSERIES accessories include:

- Spare relay
- Base
- Partition plates
- Cross-connections
- Power-feed modules

**General ordering data**

|            |                             |
|------------|-----------------------------|
| Type       | ZQV 1.5N/R6.4/19 SW         |
| Order No.  | <a href="#">1391600000</a>  |
| Version    | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118191806               |
| Qty.       | 10 pc(s).                   |

**TERMSERIES**  
**ZQV 1.5N/R6.4/19 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 119 mm  | Width (inches)  | 4.685 inch |
| Height     | 13.1 mm | Height (inches) | 0.516 inch |
| Depth      | 4.9 mm  | Depth (inches)  | 0.193 inch |
| Net weight | 4.65 g  |                 |            |

**Temperatures**

|                             |                |                             |                |
|-----------------------------|----------------|-----------------------------|----------------|
| Operating temperature, max. | 60 °C          | Operating temperature, min. | -40 °C         |
| Storage temperature, max.   | 85 °C          | Storage temperature, min.   | -40 °C         |
| Operating temperature       | -40 °C...60 °C | Storage temperature         | -40 °C...85 °C |

**Cross-connection data**

|                 |                      |                                  |         |
|-----------------|----------------------|----------------------------------|---------|
| Rated voltage   | 250 V                | Rated current                    | 17.5 A  |
| Insulation      | Yes                  | Electric shock protection        | Yes     |
| Colour          | Black                | No. of cross-connected terminals | 19      |
| Pitch in mm (P) | 6.4 mm               | Type of mounting                 | Plugged |
| Version         | can be cut to length |                                  |         |

**General data**

|                           |                      |        |       |
|---------------------------|----------------------|--------|-------|
| Version                   | can be cut to length | Colour | Black |
| UL 94 flammability rating | V-0                  |        |       |

**Insulation coordination**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Connection data**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 6.4 mm |
|-----------------|--------|

**Rated data UL**

|                    |      |
|--------------------|------|
| Rated current (UL) | 10 A |
|--------------------|------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | ETIM 5.0   | EC000489    |
| ETIM 6.0   | EC002586    | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-37-92-08 | eClass 8.1 | 27-37-92-08 |
| eClass 9.0 | 27-37-16-92 | eClass 9.1 | 27-37-16-92 |

**Approvals**

Approvals



ROHS

Conform

### TERMSERIES ZQV 1.5N/R6.4/19 SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                    |                                         |
|--------------------|-----------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 4.2 ELECTR 18/19 EN</a> |
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>            |
| User Documentation | <a href="#">Operating Instructions</a>  |

## TERMSERIES ZQV 1.5N/R6.4/19 SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensional drawing

