

**SAK Series**  
**AP AKZ4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	AP AKZ4
Order No.	<a href="#">0294460000</a>
Version	SAK Series, End plate, 1.5 mm, Beige, Direct mounting
GTIN (EAN)	4008190466268
Qty.	20 pc(s).

**SAK Series**  
**AP AKZ4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	1.5 mm	Width (inches)	0.059 inch
Height	27 mm	Height (inches)	1.063 inch
Depth	24.5 mm	Depth (inches)	0.965 inch
Net weight	1.15 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	PA 66	Colour	Beige
UL 94 flammability rating	V-2		

**System specifications**

Version	End plate
---------	-----------

**Additional technical data**

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

**Classifications**

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-33
eClass 9.1	27-14-11-33		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>