

**A-series
AEB 35 SC/1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	AEB 35 SC/1
Order No.	1991920000
Version	A-series, End bracket
GTIN (EAN)	4050118376722
Qty.	50 pc(s).

**A-series
AEB 35 SC/1**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	8 mm	Width (inches)	0.315 inch
Height	58 mm	Height (inches)	2.283 inch
Depth	36 mm	Depth (inches)	1.417 inch
Net weight	13.32 g		

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	WEMID GF 30	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals	Tightening torque (mounting screw)	1...1.2 Nm
Mounting rail	TS 35		

Additional technical data

Installation advice	Direct mounting	Interlock	for screw fixing
Open sides	closed	Snap-on	No
Type of mounting	Screwed	With snap-in pegs	No

Classifications

ETIM 6.0	EC001041	eClass 6.2	27-14-11-35
eClass 9.1	27-14-11-35		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S