

Connecting elements
H2,5/19D ZH BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in poly-bag
- DIN colour code
- other colour code

General ordering data

Type	H2,5/19D ZH BL
Order No.	9037500000
Version	Wire end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, Blue
GTIN (EAN)	4008190493073
Qty.	500 pc(s).
Packaging	loose

Connecting elements
H2,5/19D ZH BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	19 mm	Width (inches)	0.748 inch
Net weight	0.29 g		

Technical data

Version	Twin wire-end ferrule
---------	-----------------------

Wire-end ferrules

Collar height (A)	8 mm	Collar width (B)	4.5 mm
Colour code	DIN	Conductor cross-section	2.5 mm ²
Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	10 mm
L1 in mm	19 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.4 mm	Stripping length	13 mm
Wire connection cross section AWG, max.	AWG 14		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S

Data sheet

**Connecting elements
H2,5/19D ZH BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

