



Sockets

SEP 2630 S1,9



Product	SEP 2630 S1,9
description	Gold-plated brass safety press-in socket, 4 mm diameter, contact-protected, with 1.9 mm soldering spike. For installation into switchpanels with wall thicknesses between 1 mm and 10 mm. Accessory BES 1000. Installation hole: 12.2 +/-0.1 mm diameter. Entry chamfer 0.5 x 45 degree.
operating instruction	BA454
article-no. / *colour	9723631xx 
drawing	
technical data	
connection	solder connection
rated voltage ⁽¹⁾	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current ⁽¹⁾ (consider derating curve)	24 A
material socket	brass, gold plated
housing material	PA
temperature range acc. To IEC61010 ⁽²⁾	-40 °C to +80 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	V-2

4 mm safety system

standard	IEC 61010
----------	-----------

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

stand: 20.07.2018