BIT SETS

148-PC MASTER BIT SET

• Huge assortment of popular and hard-to-find bits for a wide range of applications.

		3 - 1 - 1 - 1			
Phillips	1"	#00 (3), #0 (3), #1 (3), #2 (5), #3 (3) , #4 (3)			
	2"	#1, #2, #3 3" #1, #2 (2), #3			
Pozi	1"	#0, #1, #2 (3), #3, #4			
	2"	#2, #3 3" -			
Slotted	1"	1/8 (2), 9/64, 5/32 (2), 11/64, 3/16 (4), 7/32,			
		1/4 (4), 17/64, 9/32, 5/16"			
	2"	- 3" 3/16, 1/4"			
Star	1"	T5, T6, T7, T8, T9, T10, T15, T20, T25, T27,			
		T30, T40, T45 (also as Tamper Resistant)			
	2"	T10, T15, T20, T25, T27, T30, T40			
Square	1"	S1, S2 (2), S3			
	2"	S2 3" S1, S2 (2), S3			
Hex	1"	1/16 (2), 5/64 (2), 3/32 (2), 7/64 (2),			
		1/8, 9/64, 5/32, 3/16, 7/32, 1/4"			
	2"	3/16, 7/32, 1/4"			
	1"	1.5 (2), 2 (2), 2.5 (2), 3 (2), 4, 5, 5.5, 6, 8mm			
Spline	M5, M6, M8				
Spanner		#4, #6, #8, #10			
Tri Wing	1"	#1, #2, #3, #4			
Four Wing		#6, #8, #10			
Clutch		C1, C2, C3			



101-PC RATCHETING BIT DRIVER SET

- Hi-torque ergonomic cushion grip ratcheting screwdriver.
- High quality S2 alloy steel bits for superior strength & durability. Includes 1/4" drive socket adapter (1" and 2"), 1" wing nut driver, 2-1/4" magnetic bit holder, 1" coupler.

Phillips	1"	#0 (2), #1 (2), #2 (3), #3 (2)				
Pozi	1"	#0, #1 (2), #2 (3), #3 (2)				
Slotted	1"	3, 4, 5, 6mm				
Star	1"	T8, T10 (2), T15 (2), T20 (2), T25 (2), T27, T30, T40,				
		T45				
Tamper Resistant	'	T8, T10, T15, T20, T25, T27, T30, T40, T45				
Square	1"	S0, S1, S2, S3				
Hex	1"	1/16, 5/64, 3/32, 7/64,1/8, 9/64, 5/32, 3/16, 7/32, 1/4"				
		1.5, 2, 2.5, 3, 4, 4.5, 5, 5.5, 6mm				
Tamper	1"	5/64, 3/32, 7/64,1/8, 9/64, 5/32"				
Resistant		2, 2.5, 3, 4, 5, 6mm				
Spline		M5, M6, M8				
Spanner		#4, #6, #8, #10				
Tri Wing	1"	#1, #2, #3, #4				
Four Wing		#6, #8, #10				
Clutch		C1, C2, C3				

ltem #	II.	IVIP	PKG	
W1719	6	12	DBL	

29-PC QUICK CHANGE DRIVER SET

- Chrome vanadium steel construction.
- Heat treated for longer life.
- 3-3/16" magnetic screw guide with retracting sleeve.

1"	#1, #2 (4), #3
2"	#2
1"	#2, #3
1"	6-8, 8-10, 10-12
1"	T10, T20, T30
1"	S1 (2), S2 (4), S3 (2)
2"	S2
1"	1/4, 5/16"
	2" 1" 1" 1" 1" 2"

Item #	ΙP	MP	PKG
W9024	6	24	DBL





