

RATCHETING CLAMPS

- High strength rubber grip nylon handle.
- Quick release trigger allows for fast and easy operation.
 Pivoting soft jaws with V-groove for round applications.

						Throat	Clamping
Item #	IP	MP	PKG	Length	Opening	Depth	Pressure
W5090	12	120	TAB	5"	1-1/2"	1-3/4"	17 lbs.
W5091	12	120	TAB	6-1/4"	2"	2-1/4"	33 lbs.
W5092	12	96	TAB	9"	3"	3-3/4"	55 lbs.



METAL SPRING CLAMPS

- Heavy duty spring for extra gripping power.
- Corrosion resistant nickel plating.
- Non-marring rubber tips.

						Clamping
Item #	ΙP	MP	PKG	Length	Opening	Pressure
W5081	18	108	BLK	1"	1"	3.5 lbs.
W5082	12	72	BLK	6"	2"	4.5 lbs.
W5083	8	32	BLK	9"	3"	6.5 lbs.
W5080 4-PC	12	48	CRD	2"	1/2"	2.5 lbs.




- Heavy duty fiberglass reinforced nylon body.
- Non-maring swivel pads at the ends to adjust to irregular shapes.
- Inner gripping teeth for larger clamping applications.

					Throat		Clamping
Item #	IP	MP	PKG	Length	Depth	Opening	Pressure
W5088	50	400	TAB	2"	3/4"	1/2"	1.5 lbs.
W5087	50	400	TAB	3"	1"	1"	2 lbs.
W5089	6	72	BLK	3"	1"	1"	2lbs.

PIPE CLAMPS

• The quick release four plate clutch produces up to 1,950 pounds of clamping pressure.

 Cast steel construction provide durability for years of service.



Item #	IP	MP	PKG	Pipe (NPT)	Throat Depth	Clamping Pressure
W3960	6	24	CLM	1/2"	3/4"	1,250 lbs.
W3961	6	24	CLM	3/4"	3/4"	1,950 lbs.

LOCKING C-CLAMP

- Heavy duty construction.
- Quickly adjusts to right size before use.
- Locks to work with squeeze of one hand.
 Unlocks easily by squeezing release lever.

Item #	IP	MP	PKG	Length	Capacity
W5100	6	48	SLV	6"	2"
W5101	6	48	SLV	8"	2-3/8"
W5102	6	24	SLV	11"	3-1/2"



