

9-PC HOOK & PICK SET

- Drop forged, heat-treated chrome vanadium steel shafts.
- Comfortable non-slip molded grips.
- Includes 1" scraper.
- US Patent D693201S1



Item #	IP	MP	PKG	Length	Contents
W948	1	6	CRD	10"	Straight, full hook, 45, 90, hook, scraper
				6-1/2"	Straight, full hook, 45, 90, hook

6-PC HOOK & PICK SET

- Includes straight, angled and combination picks.
- Durable double injection molded handles.
- Handy storage tray included.



Item #	IP	MP	PKG	Length	Contents
W942	6	48	CRD	9-3/8"	Straight, 90°, hook, double angle, complex, combination pick.



8-PC SPECIALTY PICK/DRIVER SET

- Chrome vanadium steel shafts with magnetic tips.
- High visibility PVC handles.



Item #	IP	MP	PKG	Length	Picks	Drivers
W941	6	24	CRD	5-1/4"	Straight, 45°, 90°, hook	#0, 1/8", T15, T20

2-PC SPECIALTY PICK SET

- Hardened tips.
- Knurled center grips.
- O-ring and seal pick for removing and installing o-rings and seals.



Item #	IP	MP	PKG	Length	Contents
W80750	24	144	CRD	9"	Straight, 90°, hook, double angle



9-PC INSPECTION SET

- Versatile utility kit for automotive access, inspection, removal and retrieval
- 3 LED anodized aluminum flashlight features 1/4" hex holder.
- Mirror and pickup tool extend to nearly 20"
- Batteries included.



Item #	IP	MP	PKG	Mirror	Lift	Telescoping		Battery		Picks	Drivers
				Diameter	Capacity	Min	Max	Qty.	Type		
W949	6	36	DBL	1-1/8"	3 lbs.	5-3/4"	20"	4	LR44	Straight, 90°, hook, double angle	#0, 1/8"

HAND TOOLS