

KEMET, FX5, Flex Suppressors, Commercial Grade



General Information

| | |
|------------------------|--|
| Series: | FX5 |
| Style: | Sheet |
| Description: | Flex Suppressor High Permeability Type |
| Features: | High Permeability Type |
| RoHS: | Yes |
| Qualifications: | UL94 HB, UL File No. E176124 |
| Environment: | RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

Dimensions

| | |
|-------------------|-------------|
| Sheet Size | 240x50mm |
| L | 240mm NOM |
| W | 50mm NOM |
| T | 0.025mm NOM |

Specifications

| | |
|-------------------------------|-----------------|
| Temperature Range: | -40/+105C |
| Magnetic Permeability: | 150 TYP At 3MHz |
| Effective Frequency: | 10 GHz MAX |
| Resistance: | 1 MOhms MIN |
| Specific Gravity: | 3.3 Atm TYP |

Packaging Specifications

| | |
|--------------------------|--------------------------|
| Tape Description: | Without PET Tape (Txx00) |
| Tape Thickness: | 0.01mm |
| Weight: | 2.2854 kg |