

BNC Male to 4mm Binding Posts



Description

BNC male to 4mm binding posts adapts BNC female cable components or equipment to double binding posts. Connections can be made to the binding posts by spade lugs, banana plugs or wire leads.

Specifications

Voltage Max.	500 Vrms
Current Max.	3 A
Impedance	50 Ω
Temperature	0° to +50°C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website:
caltestelectronics.com *Technical data subject to change.* © Cal Test Electronics 2018.
caltestelectronics.com

