



DATA SHEET

CODE:
OL 20027

WATERPROOF BOX IP66 SMOOTH WALLS – IP66 - GREY – WITH NYLON SCREWS



Mounting bracket



Lid opening



Fixing set for OL 20027

Technical features

Internal dimensions	456x380x121 mm
Degree of protection	IP66
IK grade	IK06
Heat resistance	Glow wire 650°C
Color	Grey RAL 7035
Installation temperature	Max= +60°C – min.= -25°C
Cover Screws	4 (with sealable zip)
Material	ABS (stabilized UV) - Halogen & PVC free
Norm	EN 60670-1:2005 EN 60670-22:2006
Norm Test IK	EN 62262