



SLLP14-910P88

▶ LS SERIES FULL FEATURE HEAVY-DUTY TYPE 4 SAFETY LIGHT CURTAINS



EZ-SCREEN LS, Pair

Resolution: 14 mm; Range: 12 m (40 ft)

Defined Area: 910 mm (35.8 in.); Housing: Yellow

Connection: M12 8-pin 300 mm Pigtail QD; 2x OSSD, EDM, Fault Out & Fault Reset

Part Number: 89675

CERTIFICATIONS



SPECIFICATIONS

Primary Housing Material	Aluminum
Safety Level	Type 4
Effective Aperture Angle	Type 4 Per IEC 61496-2
Connector Type	M12 Pigtail (Yellow)
Defined Area (mm)	910
Dimensions WxD (mm)	36 x 45
Overall Length (mm)	914
External Monitoring Device	1 Channel
Cookies: By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our privacy policy.	
Housing Finish	Yellow Polyester

IP Rating	IP65; IP67
Number of Pins (Receiver/Emitter)	8
Operating Distance (m)	0.1 - 12
Operating Voltage	24 V dc +/- 15%
Operating Temperature	-20 to +55 deg. C; RH 95%
PL Rating	PLe
Recovery Time	116 / 391
Resolution (mm)	14
Reduced Resolution	No
Response Time	26.9
SIL Rating	SIL3; CL3
Electrical Safety Class	III
Scan Code	Selectable
Shock	10g at 16ms (6000 cycles)
Short Protection	Yes
System Type	Emitter/Receiver Pair
Vibration	10-55 Hz at 0.35 mm
Auxiliary Output	No
Fault Output	Yes
Housing Material	Aluminum; Zinc; Acrylic
OSSD Rating	24 V dc at 0.5 A each
Supply Current	115 mA Typical
Trip/Latch Output	Trip
Test Input	No
Feature: End-to-End Sensing	Yes
Feature: ESD Safe	No
Feature: Integral Muting	No






Cookies: By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our privacy policy.

RELATED PRODUCTS

DOUBLE ENDED CORDSETS

	<p>DEE2R-81D</p> <p>Euro-style Quick-Disconnect Cable ; 8 Pin Double Ended With 1 Female & 1 Male Connector; 0.3 m (1 ft) in Length; 22 GA Cascadeable</p>
	<p>DEE2R-83D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 0.91 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-812D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8-pin Male Connector Straight; 8-pin Female Connector Straight; 3.66 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-815D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 4.57 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-825D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 7.62 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-830D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 9.14 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-850D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 15.24 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-875D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 22.86 m Length; Chrome plated brass coupling nut</p>
	<p>DEE2R-8100D</p> <p>Euro-style Quick Disconnect Cable; Double-ended; 8 Pin Male Connector Straight; 8 Pin Female Connector Straight; 30.48 m Length; Chrome plated brass coupling nut</p>


Cookies: By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our [privacy policy](#).

	<p>QDE-815D</p> <p>Euro-Style Quick Disconnect Cable; 8 Pin Euro-Style Female Connector; 5 m (15 ft) in Length; Non-Shielded</p>
	<p>QDE-825D</p> <p>Euro-Style Quick Disconnect Cable; 8 Pin Euro-Style Female Connector; 8 m (25 ft) in Length; Non-Shielded</p>
	<p>QDE-850D</p> <p>Euro-Style Quick Disconnect Cable; 8 Pin Euro-Style Female Connector; 15 m (50 ft) in Length; Non-Shielded</p>
	<p>QDE-875D</p> <p>Euro-Style Quick Disconnect Cable; 8 Pin Euro-Style Female Connector; 23 m (75 ft) in Length</p>
	<p>QDE-8100D</p> <p>Euro-Style Quick Disconnect Cable; 8 Pin Euro-Style Female Connector; 30 m (100 ft) in Length; Non-Shielded Cable</p>


SPLITTER CORDSETS

	<p>CSB-M1280M1280</p> <p>Euro-style Quick Disconnect Splitter Connector; 8-Pin Male Trunk Straight; 8-Pin Female Straight Branches (2); Black PUR Splitter Junction Cable</p>
	<p>CSB-M1281M1281</p> <p>Euro-style Quick Disconnect Splitter Cable; 8 Pin Double-ended with 0.3 Female Branches and; Male Rotatable Trunk Connector; 0.3 m Trunk Length ; 8X22 GA 1 Ft Trunk 1 Ft Branch</p>
	<p>CSB-M1288M1281</p> <p>Euro-style Quick Disconnect Splitter Cable; 8 Pin Double-ended with 0.3 Female Branches and ; Male Rotatable Trunk Connector; 2.5m Trunk Length; 8X22 GA 8 Ft Trunk 1 Ft Branch</p>
	<p>CSB-M12815M1281</p> <p>Euro-style Quick Disconnect Splitter Cordset; 8-Pin Male Straight Trunk ; 4.6 M (15ft) in length; 8-Pin Female Straight Branches (2); 0.3 m (1 ft) in length; Black PUR Splitter Junction; Yellow PVC Cable Jacket</p>
	<p>CSB-M12825M1281</p> <p>Euro-style Quick Disconnect Splitter Cable; 8 Pin Double-ended With 0.3 Female Branches and; Male Rotatable Trunk Connector; 8 m Trunk Length; 8X22 GA 25 Ft Trunk 1 Ft Branch</p>


Cookies: By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our [privacy policy](#).

	<p>CSB-UNT825M1281</p>
<p>Euro-style Quick Disconnect Splitter Cable; 8 Pin; 0.3 m Female Branches Unterminated Trunk; 8 m (25 ft) in Length; 8X22 GA 25 Ft Trunk 1 Ft Branch</p>	





ADAPTERS, BRACKETS, CLAMPS AND MOUNTING ACCESSORIES

	<p>EZLSA-MBK-11</p>
<p>EZ-SCREEN LS Accessory Bracket: End Mount; Includes Two Brackets and Hardware; Rotation: 360 Degrees in 23 Degree Increments; 8 ga. Steel, Black Zinc Plated</p>	

ENCLOSURES - SAFETY LIGHT

	<p>EZLSA-TE-910</p>
<p>Accessory: Tubular Enclosure for EZ Screen LS; Length 910 mm</p>	

SGS AND LS MUTING ARM KITS

	<p>SGSA-ML-L-LPQ20</p>
<p>Safety Grid System and LS Light Curtain, Accessory; Mute Arm Kit: L Configuration Left Side; Includes: One Sensor Arm with Two Q20PLPQ5 Sensors Installed; One Reflector Arm with Two Reflectors Installed, and Mounting Hardware</p>	
	<p>SGSA-ML-R-LPQ20</p>
<p>Safety Grid System and LS Light Curtain, Accessory; Mute Arm Kit: L Configuration Right Side; Includes: One Sensor Arm with Two Q20PLPQ5 Sensors Installed; One Reflector Arm with Two Reflectors Installed, and Mounting Hardware</p>	
	<p>SGSA-MT-LPQ20</p>
<p>Safety Grid System and LS Light Curtain, Accessory; Mute Arm Kit: T Configuration; Includes: Two Sensor Arms with Two Q20PLPQ5 sensors installed on each arm; Two Reflector Arms with Two Reflectors Installed on Each Arm, and Mounting Hardware</p>	
	<p>SGSA-MX-LPQ20</p>
<p>Safety Grid System and LS Light Curtain, Accessory; Mute Arm Kit: X Configuration; Includes: Two Sensor Arms with One Q20PLPQ5 Sensor Installed on Each Arm; Two Reflector Arms with One Reflectors Installed on Each Arm, and Mounting Hardware</p>	

Cookies: By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our [privacy policy](#).



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America

Cookies: By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our privacy policy.