


**Model 3752 BNC (F) To BNC (M)  
Miniature Size Aluminum Box  
With Cover**



**MATERIALS:**

Connector: BNC (F) to BNC (M)

Body: Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Solder Turret Terminal Screws: Steel 4 each #4-40

Shielded Housing: Die cast aluminum, Alloy A380 or A384.

Finish: Blue baked enamel per Federal Standard 595 #25109 over Phosphoric Etch per MIL-C-15328.

Cover: .040 thick aluminum 1100-H14

Finish: Clear anodized per MIL-A-8625.

Screws: 4 each 2-32 x 6.35 (1/4") Pan head, self-tapping. Steel

**RATINGS:**

Operating Voltage: Inner Conductor/Shield: 500 VRMS Max.

Operating Temperature: -55°C to +150°C

Nominal Impedance: 50 Ohms

**ORDERING INFORMATION:** Model 3752

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA