

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212010003](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Black Nitrile Gasket, Un-Mounted, Bulk Pack

Documents:

Drawing (PDF)	Product Specification TS-121201-001-001 (PDF)
Product Specification PS-121201-001-001 (PDF)	Packaging Specification PK-121201-C28-001 (PDF)
Product Specification STR-1251-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Field Attachable / Accessories
Series	121201
Form	A
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906711436

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	22.226/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	C28200N0RCN
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-121201-C28-001
Product Specification	PS-121201-001-001, STR-1251-001, TS-121201-001-001
Sales Drawing	SD-121201-003-001

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121201](#) Series