

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010179](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect Turned Crimp Contact for 16A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 2.50mm<sup>2</sup> (14 AWG), 100 per Bag

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA	256883
UL	E249674

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Contact Type	Turned Crimp Contact
Exclude SD Check	Yes
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Contacts
Product Name	GWconnect
UPC	887191874975

**Physical**

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	1.450/g
Number of Grooves	3
Packaging Type	Bag
Stripping Length	7.50mm
Wire Size AWG	14
Wire Size mm <sup>2</sup>	2.50

**Electrical**

Current - Maximum per Contact	16.0A
-------------------------------	-------

**Material Info**

Engineering Number	7300.6244.0
--------------------	-------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[93601](#) Series

**Mates With**

[93601](#) Male Turned Crimp Contact

**Use With**

S-AC, S-EC, S-EE, S-EEE, S-EHV, S-Q, S-QD, and S-M Inserts