

## CHERRY KC 6000 SLIM



Models may vary from the image shown

### Ultra-flat designer keyboard

The CHERRY KC 6000 SLIM keyboard impresses with its precise scissor mechanism, compact dimensions and state-of-the-art design. A sturdy keyboard with an integrated metal plate, it is a particularly attractive addition to the desk of the style-conscious user.

### Key benefits

- Exceptionally compact, slim housing
- High-quality scissor mechanism for perfect keystroke
- Status LEDs for the CAPS LOCK, NUM and SCROLL keys
- 6 practical additional keys
- Sturdy construction with integrated metal plate

### Technical Data:

#### Layout (country or language):

Product dependant, see table "Models"

#### Housing colour:

Product dependant, see table "Models"

#### Key colour:

Product dependant, see table "Models"

#### Weight (product):

approx. 660 g

#### Total weight (with packaging):

approx. 875 g

#### Cable Length:

approx. 1.80 m

#### Storage Temperature:

-20°C to 60°C

#### Operating Temperature:

0°C to 40°C

#### Current Consumption:

typ. 45 mA

#### Interface:

- USB

#### Product approvals:

- cURus
- CE
- FCC



#### System requirements:

- USB connection

#### Delivery Volume:

- CHERRY KC 6000 SLIM
- Operating instructions in hard copy

#### Dimensions (product):

approx. 440 x 130 x 15 mm

#### Packaging dimensions:

approx. 453 x 170 x 33 mm

#### Keyboard:

- Key technology: SX
- Service life, standard key: > 10 million key operations
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"

#### Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 20

#### Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.