AC120C Air - Cool and Comfortable

Inspired by racing cars, the AC120 Air is designed to transform your gaming room into one sleek place to be. Feel the softness of the faux leather and carbon-fibre-like seams. The pinholes in the sitting surface and the backrest of the AC120 Air allow the internal materials to breathe, keeping the chair comfortably cool even after long gaming sessions.

Key Features

Power bank and remote control batteries are not included - AC120 RGB features edge roll lighting, Aerocool's patented optic strip lighting.* We carefully selected the fibre optic strip best suited to provide the most attractive lighting and seamlessly incorporated this strip in the outer rim of the chair. * Design patented in the European Union, China and Taiwan.

Lighting Effects - The RGB system comes with four lighting effects. Set the mood of your lighting with an easy to use remote control.

Plenty of Choices - When your chair is working in the solid-colour lighting mode, you can choose from any of the 16 available preset colours the one that best fits your taste and ambience.

Light It Up - All RGB functions are powered by a USB power-bank. You can conveniently place your power-bank in the pocket below the chair.* *Power bank and remote control batteries are not included.

Air Technology - A "breathing surface" means a fresher and comfortable chair despite hours of use. Our Air Technology combines an attractive pinhole design with premium non-woven materials and foams to provide you a superior airflow that keeps you cool.

Superior Ergonomics - Paired with best ergonomics and impressive design - Aerocool gaming chairs don't just qualify as a comfy office chair, but bring all the requirements to the table as a proper gamer's chair.

Travel Neck Pillow Design - Your chair comes with a versatile neck pillow. Use it at home, while gaming, watching TV, reading, studying and napping.

Rocking Butterfly Mechanism - The chair's butterfly mechanism allows a rocking motion of up to 18°. The looseness of the mechanism can be adjusted through the spring located underneath the seat. A conveniently located lock allows setting the chair to a fixed position, if you prefer static support.

Recline 180° To Power Nap - Need just that one short power nap to boost your memory? Also improve cognitive skills, creativity and energy level? Recline to 180°, lie flat and enjoy that power nap or just stare at the ceiling, your choice.

Unique Carbon Fibre Blend - Designed for those seeking that extra oomph in their chair styles the already sporty design is complemented by a PVC cover with a unique carbon fibre look at the rear of the backrest. Attention to detail is extremely important to ensure the chair looks great from the front and the back.

2D Moveable Armrests - Set the armrests at any height and direction as you please. Movable armrests are designed to make you feel at ease while you game for hours on end.

Sturdy and Reliable - Class-4 hydraulic lift supports up to 150Kg.

Specifications

Model Name: AC120 Air RGB

Chair Type: Gaming Chair

Foam Type: Injection Moulded

Foam Density: 50 / Seat 45 / Back

Frame Colour: Black
Frame Construction: Metal
Chair Cover Colour: Black

Chair Cover Material: Carbon PVC + High Quality PU

Adjustable Armrests: 2D (2-Directional)

Mechanism Type: Butterfly

Rocking Ranges: 3 - 18°

Tilt Lock: Yes

Tilt Angle Lock: N/A

Gas Lift Specification: 80mm

Gas Lift Class: 4

Chair / Backrest Style: Middle **Adjustable Back Angle:** 90° - 180°

Adjustable Headrest: Yes

Base Type: 350mm Matt Colour Metal Base

Caster Size & Material: 65mm / Nylon

Assembly Required: Yes

Seat Size: 53 x 57 x 14cm (W x D x H)

Warranty Period: 2 Years

Weight Bearing: < 150 KGs

Recommended User Height: < 2.00M

Recommended User BMI: < 25

Connector: USB

Powered By: Power Bank (Not Included)

Lighting Control: Remote Controller (Battery Not Included)

Manufacturer Part Number: ACGC-2012111.11

EAN Number: 4710700950432

Has Mains Plug: No

Colour: Black

Chair

What's In The Box: Screws

Allen Wrench

Unit (Product) Dimensions (mm): 700mm x 1240mm x 770mm (W x H x D)

Packaging Dimensions (mm): 700mm x 330mm x 860mm (W x H x D)

Net Weight (KGs): 20 KGs

Gross Weight (KGs): 23 KGs