

IP68 waterproof and dustproof smartphone with 4G support, 5.0 HD IPS screen and 13.0MP camera



Waterproof



HD IPS Display
Gorilla Glass 3



16 GB eMMC



LTE-A



13.0Mpx AF
with Flash



4000mAh battery

- IP68 waterproof and dustproof: protected body perfect for extreme conditions
- Wide screen: high-precision 5.0" HD IPS screen protected with Gorilla Glass 3
- Speed in your palm: 4G LTE Internet connection gives you ability to do more: streaming without interruption, seamlessly playing multi-player games and browsing faster than ever before

- Photo and video: advanced 13.0MP AF camera with LED-flash ensures excellent clear & vivid shots
- High performance multitasking and energy saving: based on 64-bit quad core processor and 2GB RAM
- Capacious: 16GB of internal storage on board and possibility to expand it with microSD cards up to 32GB
- Dual SIM: for optimizing budget on calls and Internet

SIM card slot	Dual SIM: LTE + WCDMA
Display	Size: 5.0" Resolution: HD (720x1280) Technology: IPS, Gorilla Glass 3
Processor	MT6737 1.3 GHz 64-bit quad core
Memory	Built-in: 2 GB RAM + 16 GB eMMC Expandable: slot for microSD™ card up to 32GB
Power	4000 mAh Li-ion battery
OS	Android 7.0 Nougat
Imaging	Front: 2.0MP Rear: 13.0MP AF with flash light

Network	4G LTE: 800/1800/2600 MHz 3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900MHz
Connectivity	BT 4.0+HS, Wi-Fi: 802.11b/g/n USB: microUSB 2.0
Audio	Mic, speakers, 3.5 jack
Built-in devices	GPS, FM
Dimensions	147 x 76 x 12.7 mm
Weight	210g (with battery)
In the box	USB cable, AC charger, screen protective film