

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Crimp contact, contact diameter: 0.6 mm, turned, Pin, contact material: CuZn, contact surface: Ni/Au, connection cross section: 0.14 mm² ... 0.34 mm² AWG 26 ... 22



Key Commercial Data

Packing unit	100 STK
Minimum order quantity	100 STK
GTIN	4 055626 368108
GTIN	4055626368108
Weight per Piece (excluding packing)	0.080 g
Custom tariff number	74152900
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C 85 °C
---------------------------------	--------------

Mechanical characteristics

Conductor cross section	0.14 mm² 0.34 mm² (flexible)
Connection cross section AWG	26 22 (flexible)
Stripping length of the individual wire	4 mm +0,5 mm
Contact diameter	0.6 mm
Insertion/withdrawal cycles	≥ 100

General

Туре	Individual male contact
Connection method	Crimp connection
Contact type	turned



Technical data

Material data


Contact material	CuZn
Contact surface material	Ni/Au

Environmental Product Compliance

REACh SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Crimp contact, diameter: 0.6 mm

Classifications

eCl@ss

eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

ETIM

ETIM 5.0	EC000796
ETIM 6.0	EC000796

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details



Approvals

EAC

EHE

EAC-Zulassung

Accessories

Accessories

Circular connector (cable-side)

Connector - SACC-M12MSX-8CT-CL SH - 1422844



Connector, Ethernet/PROFINET CAT6 $_{\rm A}$ (10 Gbps), 8-position, shielded, Plug straight M12, X-coded, Crimp connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 6.5 mm ... 10 mm, without crimp contacts

Connector - SACC-M12MRX-8CT-CL SH - 1422845



Connector, Ethernet/PROFINET CAT6 $_{\rm A}$ (10 Gbps), 8-position, shielded, Plug angled M12, X-coded, Crimp connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 6.5 mm ... 10 mm, without crimp contacts

Connector - SACC-P12MSX-8CT-CL SH - 1021783



Connector, Ethernet/PROFINET CAT6_A (10 Gbps), 8-position, shielded, Plug straight M12 Push-Pull, X-coded, Crimp connection, knurl material: PA 6.6, external cable diameter 6.5 mm ... 10 mm, without crimp contacts

Connector - SACC-P12MRX-8CT-CL SH - 1021784



Connector, Ethernet/PROFINET CAT6_A (10 Gbps), 8-position, shielded, Plug angled M12 Push-Pull, X-coded, Crimp connection, knurl material: PA 6.6, external cable diameter 6.5 mm \dots 10 mm, without crimp contacts

Crimping tool



Accessories

Crimping pliers - CRIMPFOX-TC MP - 1212510



Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

Phoenix Contact 2018 @ - all rights reserved http://www.phoenixcontact.com