

PT-E110VP FEATURES



Compliant labelling in the palm of your hand

Ensuring compliance with electrical regulations (IET 17th Edition) is critical for electrical installers/contractors. The P-touch E110 prints on durable labels ideal for identification of plug and switch faceplates, cables, conduits and consumer units.

Common labelling tasks can be completed easily thanks to the dedicated quick-access buttons and the standard PC QWERTY keyboard layout. With 200 symbols to choose from several categories including electrical, datacomms and audio/video, customise your labels as needed using the easy-to-read graphic LCD.

As many installations use numbers to identify plugs, switches and faceplates, the dedicated numeric keyboard means you can type with one finger. And the serialise function lets you print multiple labels while automatically incrementing the number, such as A001, A002, A003.

PT-E110VP FEATURES

General

Carton contents (PT-E110VP)	PT-E110 labelling machine 9mm TZe black on white tape flexible ID tape cassette (8m) AC adapter Carry case Documentation
Language support	English, German, French, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

Dimensions & Weights

Without carton	111 (w) x 58 (d) x 204 (h) 0.4kg
With carton (PT-E110VP)	314 (w) x 116 (d) x 279 (h)

Built In Features

Keyboard	PC style QWERTY/QWERTZ/AZERTY
Dedicated number keypad	Yes
Display type	Graphic Monochrome LCD with label preview capability
Display resolution	16 characters by 1 lines 128 x 16 dots
Printing speed	Up to 20mm/second
Print resolution	180dpi
Maximum print height	9 mm
Cutter type	Manual cutter
Label length	30mm minimum 300mm maximum
Maximum lines per label	2
Tape margins	Full, Half, Narrow, Chain Print
Vertical text printing	Yes
Mirror printing	No
Copies	1 to 9
Automatic numbering	Yes (1 – 50)

Label Creation

Smart label application keys	General, Faceplate, Cable Wrap, Cable Flag
Fonts	1 Helsinki
Font styles	7 (excl. Normal) Normal, Bold, Outline, Shadow, Italic, Italic Bold, Italic Outline, Italic Shadow
Font sizes	16, 22, 28, 42, 56 point
Symbols	200
Frames	1 Rectangle with rounded corners

Memory

Label memory locations	9 (up to 720 characters total maximum)
-------------------------------	--

Supplies

Tape types	TZe
Tape widths	TZe: 3.5, 6, 9 & 12

Optional Accessories

Tape Cutter	TC-4
AC adaptor	AD-24ES