

## Han M23 cover-s met. for HBM, chain 100mm

and the second s		Part number	09 15 600 9102
		Specification	Han M23 cover-s met. for HBM,chain 100mm
		HARTING eCatalogue	https://b2b.harting.com/09156009102
		Identification	
		Category	Hoods/Housings
		Series of hoods/housings Han <sup>®</sup> M23 Power	
		Type of hood/housing	Cover
		Description of hood/ housing	for bulkhead mounted housings for cable to cable housing With chain (70 mm)
Version			
Size	M23		
Technical characteristics			
Limiting temperature	-40 +125 °C		
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 in locked position		
Material properties			
Material (hood/housing)	Copper-zinc alloy		
Surface (hood/housing)	Nickel plated		
Specifications and approvals			
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076		
Commercial data			
Packaging size	5		
Net weight	11.72 g		
Country of origin	Germany		

Page 1 / 1 | Creation date 2018-08-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com